



A	Skin	Size
	29" (736.6mm)	W
		H
1x1 Flat Front <small>1x1 Flat Front Shown as it will appear on the Xpressions unit</small>		

B	Skin	Size
	29" (736.6mm)	W
		H
1x1 Flat Front <small>1x1 Flat Front Shown as it will appear on the Xpressions unit</small>		

C	Skin	Size
	29" (736.6mm)	W
		H
1x1 Flat Front <small>1x1 Flat Front Shown as it will appear on the Xpressions unit</small>		

D	Skin	Size
	40.5" (1028.7mm)	W
		H
Diamond <small>Diamond Shown as it will appear on the Xpressions unit</small>		

E	Skin	Size
	91" (2311.4mm)	W
		H
3x1 Double Thread <small>3x1 Horizontal Double Thread Shown as it will appear on the Xpressions unit</small>		

F	Skin	Size
	29" (736.6mm)	W
		H
1x3 Vertical Double Thread <small>1x3 Vertical Double Thread Shown as it will appear on the Xpressions unit</small>		
1x3 Double Thread		

G	Skin	Size
	29.5" (749.3mm)	W
		H
1x1 Single Twist <small>1x1 Single Twist Shown as it will appear on the Xpressions unit</small>		

H	Skin	Size
	29" (736.6mm)	W
		H
1x1 Flat Back <small>1x1 Flat Back Shown as it will appear on the Xpressions unit</small>		

I	Skin	Size
	29" (736.6mm)	W
		H
1x1 Flat Back <small>1x1 Flat Back Shown as it will appear on the Xpressions unit</small>		

It is recommended that all text and borders be 2" from the finish size

Focus Area Key
 focus area is always 3"-5" inside edge of all four sides on all skin styles and sizes